



YAZ6C2TC38, Compression Terminal, 6 AWG Cu, 2-Hole, 3/8" Stud, 1" Spacing, Long Barrel

By Burndy
Catalog # YAZ6C2TC38

6 AWG, CU, 2 Hole, 3/8 Stud, 1 IN Spacing, Long Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Yes
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	• Buy America Compliant (All status valid till December 2026) • Buy American Act Compliant (All status valid till December 2026) • BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	6 AWG
Conductor Size	6 AWG
Conductor - Copper Str Navy Size	30 (19) Navy
Conductor Type	CODE

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2



Connector TypeLONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.58 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	82 mm
Dimension - Outside Diameter inch	0.29 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1-3/16
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-1/8 in
Dimension - Z inch	0.43 in
Dimension - B Length inch	1.12 in
Dimension - N inch	0.41 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	3.22 in

General

Trade Name	HYLUG™
Die Index	7
Feature - Barrel Type	Long
Feature - Barrel Style	Skived
Plated	Y
Color Code	Blue
Physical Attribute - Tongue Type	Standard
Sub Brand	HYLUG
UPC	781810224298

Type	Long Barrel, Skive, Tin Plated	Minimum Pack Quantity	1
Material	Copper	Carton Quantity	50
Plating Type	Tin - Electro Plated		
Finish Type	Tin-Plated		
UPC 12 Digit	781810224298		
UPC 14 Digit GTIN	00781810224298		

Product Assets

- Catalog [English]
- Installation Manual [English]
- Installation Manual [French, English]

Logistics



A Hubbell brand