



YAZ6CTC1445, Compression Terminal, 6 AWG Cu, 1-Hole, 1/4" Stud, Long Barrel, 45 Degree

By Burndy

Catalog # [YAZ6CTC1445](#)

6 AWG CU, One Hole, 1/4 Stud Size, Long Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Blue Color Code, 7 or 374 Die Index.

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

General

Catalog Number	YAZ6CTC1445
Color Code	Blue
Connector Type	LONG BARREL
Die Index	7
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Skive, Tin Plated
UPC	781810239360
UPC 14 Digit GTIN	00781810239360

Dimensions

Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	1.12 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - Height inch	1.19 in
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm



Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.82 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.29 in
Dimension - Pad Width inch	0.45 in
Dimension - Strip Length inch	1-3/16
Dimension - Stud Size fraction	1/4
Dimension - Z (inch)	0.33 in
Physical Attribute - Tongue Angle	45 Degree

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	30 (19) Navy
Conductor - Copper Str Size	6 AWG
Conductor - Material	COPPER
Conductor Size	6 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	50
Minimum Pack Quantity	50

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SE..212356-04](#)
[Specifications - YAZ6CTC1445](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-YAZ6CTC1445-SPEC-EN | REV 3/2025