



YAZ6CTC38, Compression Terminal, 6 AWG Cu, 1-Hole, 3/8" Stud, Long Barrel

By Burndy
Catalog # [YAZ6CTC38](#)



6 AWG CU, One Hole, 3/8 Stud Size, Long Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Blue Color Code, 7 or 374 Die Index.

Application

Wire Termination

General

Catalog Number	YAZ6CTC38
Color Code	Blue
Connector Type	LONG BARREL
Die Index	7
EU RoHS Indicator	Yes
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Skive, Tin Plated
UPC	781810239384
UPC 12 Digit	7818102393844

Dimensions

Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	1.12 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	56 mm
Dimension - Length Overall inch	2.21 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.29 in
Dimension - Pad Width inch	0.58 in
Dimension - Strip Length inch	1-3/16
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8
Dimension - Z (inch)	0.42 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	30 (19) Navy
Conductor - Copper Str Size	6 AWG
Conductor - Material	COPPER
Conductor Size	6 AWG
Conductor Type	CODE

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	50
Minimum Pack Quantity	1

Product Assets

[3D Models - YAZ6CTC38_MODEL-PDF](#)
[3D Models - YAZ6CTC38_MODEL-IGES](#)
[3D Models - YAZ6CTC38_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SE..212356-05](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YAZ6CTC38-SPEC-EN | REV 8/2024