



YAZV25TC38FX90, Compression Terminal, 1/0 Flex G,H,I,K,M, DLO, 1/0 AWG B/C, Cu, 1-Hole, 3/8" Stud, Long Barrel, 90 Degree



By Burndy
Catalog # YAZV25TC38FX90

1/0 Flex G,H,I,K,M,DLO, 1/0 AWG (B/C) CU, One Hole, 3/8 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Pink Color Code, 12 or 348 Die Index.

Application

Wire Termination

General

Catalog Number	YAZV25TC38FX90
Color Code	Pink
Connector Type	LONG BARREL
Die Index	12
EU RoHS Indicator	Yes
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Skive
UPC	781810241486
UPC 12 Digit	7818102414866

Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.50 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Height inch	2.12 in
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	31 mm
Dimension - Length Overall inch	1.22 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	1-9/16
Dimension - Stud Size fraction	3/8
Dimension - Z (inch)	0.42 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	1/0 AWG
Conductor - Copper DLO Size	1/0 AWG
Range	
Conductor - Copper Flex G Size	"1/0 AWG"
Conductor - Copper Flex G Size	1/0 AWG
Range	
Conductor - Copper Flex H Size	"1/0 AWG"
Conductor - Copper Flex H Size	1/0 AWG
Range	
Conductor - Copper Flex I Size	"1/0 AWG"
Conductor - Copper Flex I Size	1/0 AWG
Range	
Conductor - Copper Flex K Size	"1/0 AWG"
Conductor - Copper Flex K Size	1/0 AWG
Range	
Conductor - Copper Flex M	"1/0 AWG"
Size	
Conductor - Copper Str	"1/0 AWG"
Compact Size	
Conductor - Copper Str Navy	100
Size	
Conductor - Copper Str Size	"1/0 AWG"
Conductor - Copper Str Size	1/0 AWG
Range	
Conductor - CopperWeld Str	1/0 F AWG;1/0 G AWG;1/0 J
Size	AWG;1/0 K AWG
Conductor - Material	COPPER
Conductor Size	1/0 AWG
Conductor Type	CODE/FLEX
Wire Size	1/0 AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SE..212448-06](#)
[Specifications - YAZV25TC38FX90](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand