

Compression Terminal

By Burndy
Catalog # YAZV262TC38E6FX



2/0 Flex G,H,I,K,M,DLO, 2/0 AWG CU, Two Hole, 3/8 Stud Size, 7/8 Hole Spacing, Long Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Black Color Code, 13 Die Index.

Application

Wire Termination

General

| | |
|--------------------------------------|----------------------|
| Color Code | Black |
| Connector Type | LONG BARREL |
| Die Index | 13 |
| Feature - Barrel Style | Skived |
| Feature - Barrel Type | Long |
| Finish Type | Tin-Plated |
| Material | COPPER |
| Physical Attribute - Number of Holes | 2 |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Trade Name | HYLUG™ |
| Type | Long Barrel, Skive |
| UPC | 781810566343 |
| UPC 12 Digit | 7818105663433 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length inch | 1.50 in |
| Dimension - Bolt Size fraction | 3/8 |
| Dimension - Bolt Size inch | 0.38 |
| Dimension - Hole Size fraction | 3/8 |
| Dimension - Hole Size inch | 0.41 |
| Dimension - Hole Size mm | 10.4 mm |
| Dimension - L Length Overall mm | 93 mm |
| Dimension - Length Overall inch | 3.68 in |
| Dimension - Length Side B inch | 3.68 in |
| Dimension - Pad Width inch | 0.93 in |
| Dimension - Strip Length inch | 1-9/16 |
| Dimension - Stud Size fraction | 3/8 |
| Dimension - Stud Size inch | 3/8 in |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|-------------------|-------|
| Voltage - Maximum | 35000 |
| Voltage Rating | 35 kV |

Conductor Related

| | |
|--------------------------------------|-----------|
| Conductor - Copper DLO Size | 2/0 AWG |
| Conductor - Copper DLO Size Range | 2/0 AWG |
| Conductor - Copper Flex G Size | "2/0 AWG" |
| Conductor - Copper Flex G Size Range | 2/0 AWG |
| Conductor - Copper Flex H Size | "2/0 AWG" |
| Conductor - Copper Flex H Size Range | 2/0 AWG |
| Conductor - Copper Flex I Size | "2/0 AWG" |
| Conductor - Copper Flex I Size Range | 2/0 AWG |
| Conductor - Copper Flex K Size | "2/0 AWG" |
| Conductor - Copper Flex K Size Range | 2/0 AWG |
| Conductor - Copper Flex M Size | "2/0 AWG" |
| Conductor - Copper Str Compact Size | "2/0 AWG" |
| Conductor - Copper Str Navy Size | 125 |
| Conductor - Copper Str Size | "2/0 AWG" |
| Conductor - Copper Str Size Range | 2/0 AWG |
| Conductor - Material | COPPER |
| Conductor Size | 2/0 AWG |
| Conductor Type | CODE/FLEX |
| Wire Size | 2/0 AWG |

Certifications and Compliance

| | |
|------------------------------------|--------------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|----|
| Carton Quantity | 25 |
| Minimum Pack Quantity | 25 |

Product Assets

[Customer Notices - Prop 65 Notice](#)

[Installation Manuals - Copper Flex Long Terminals Tooling and Installation Instructions](#)

[Sales Drawings - 50013733](#)

[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAZV262TC38E6FX-SPEC-EN | REV 8/2023