



# YAZV27TC38FXB145, Compression Terminal, 3/0 Weld, 3/0 450/24 DLO Flex, 3/0 AWG Code, 1-Hole, 3/8" Stud, Long Barrel, 145 Degree Reverse Bend



By Burndy  
Catalog # [YAZV27TC38FXB145](#)

Cu Comp Terminal Flex Cond, 1 Hole/W/InspWindow, 3/0 Weld,3/0(450/#24)DLO Flex, 3/0 AWG Code, 600 V-35 kV, 3/8" Stud, 145° Bent(Reverse), Lng bbl, Belled End.

## Application

Wire Termination

## General

|                                      |                      |
|--------------------------------------|----------------------|
| Catalog Number                       | YAZV27TC38FXB145     |
| Color Code                           | Orange               |
| Connector Type                       | LONG BARREL          |
| Die Index                            | 14                   |
| Feature - Barrel Style               | Skived               |
| Feature - Barrel Type                | Long                 |
| Finish Type                          | Tin-Plated           |
| Material                             | COPPER               |
| Physical Attribute - Number of Holes | 1                    |
| Plated                               | Y                    |
| Plating Type                         | Tin - Electro Plated |
| Trade Name                           | HYLUG™               |
| Type                                 | Long Barrel, Skive   |
| UPC                                  | 781810511459         |
| UPC 12 Digit                         | 7818105114599        |

## Dimensions

|                                   |          |
|-----------------------------------|----------|
| Dimension - Bolt Size fraction    | 3/8      |
| Dimension - Bolt Size inch        | 0.38     |
| Dimension - Hole Size fraction    | 3/8      |
| Dimension - Hole Size inch        | 0.41     |
| Dimension - Hole Size mm          | 10.4 mm  |
| Dimension - Stud Size fraction    | 3/8      |
| Physical Attribute - Tongue Angle | Straight |

## Electrical Ratings

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 35000 |
| Voltage Rating    | 35 kV |

## Conductor Related

|                                       |   |
|---------------------------------------|---|
| Conductor - Copper DLO Size           | 2/0 AWG   |
| Conductor - Copper DLO Size Range     | 3/0 AWG   |
| Conductor - Copper Flex G Size        | "2/0 AWG"   |
| Conductor - Copper Flex G Size Range  | 3/0 AWG   |
| Conductor - Copper Flex H Size        | "2/0 AWG"   |
| Conductor - Copper Flex H Size Range  | 3/0 AWG   |
| Conductor - Copper Flex I Size        | "2/0 AWG"   |
| Conductor - Copper Flex I Size Range  | 3/0 AWG   |
| Conductor - Copper Flex K Size        | "2/0 AWG"   |
| Conductor - Copper Flex K Size Range  | 3/0 AWG   |
| Conductor - Copper Flex M Size        | "2/0 AWG"   |
| Conductor - Copper Str Compact Size   | "2/0 AWG"   |
| Conductor - Copper Str Navy Size      | 125   |
| Conductor - Copper Str Size           | "2/0 AWG"   |
| Conductor - Copper Str Size Range     | 3/0 AWG   |
| Conductor - CopperWeld Str Size       | 2/0 F AWG;2/0 G AWG;2/0 J AWG;2/0 K AWG;2/0 V AWG |
| Conductor - CopperWeld Str Size Range | 2/0 F AWG-2/0 V AWG                               |
| Conductor - Material                  | COPPER  |
| Conductor Size                        | 3/0 AWG   |
| Conductor Type                        | CODE/FLEX   |
| Wire Size                             | 3/0 AWG   |

## Certifications And Compliance

|                               |              |
|-------------------------------|--------------|
| Certification - CSA Approved  | Yes          |
| Certification - ETL           | No           |
| Certification - UL Recognized | No           |
| Certification - cULus         | No           |
| Industry Standard(s)          | UL 486A-486B |
| Standards - RoHS Compliance   | CM           |
| Status                        |              |
| UL Listed                     | Yes          |

## Logistics

|                       |      |
|-----------------------|------|
| Carton Quantity       | 20   |
| Minimum Pack Quantity | 20   |
| Pallet Quantity       | 9280 |

## Product Assets

[3D Models - YAZV27TC38FXB145\\_MODEL-PDF](#)  
[3D Models - YAZV27TC38FXB145\\_MODEL-STEP](#)  
[3D Models - YAZV27TC38FXB145\\_MODEL-IGES](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 30009546](#)  
[Specifications - YAZV27TC38FXB145](#)  
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-YAZV27TC38FXB145-SPEC-EN | REV 8/2024