

Compression Terminal

By Burndy
Catalog # [YAZV282NT38FX](#)

HYLUG™ Copper Compression Terminal; Narrow Tongue; 2-Hole with Inspection Window; Long Barrel; Accommodates: 4/0 AWG, 4/0 Weld, 4/0 (550/24) DLO; Stud: 3/8"; Stud Spacing: 1.00"



Application

Wire Termination

General

| | |
|--------------------------------------|---------------------------------------|
| Color Code | Purple |
| Connector Type | LONG BARREL |
| Die Index | 15 |
| EU RoHS Indicator | Yes |
| Feature - Barrel Style | Skived |
| Feature - Barrel Type | Long |
| Finish Type | Tin-Plated |
| Material | COPPER |
| Physical Attribute - Number of Holes | 2 |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Sub Brand | HYLUG |
| Trade Name | HYLUG™ |
| Type | YAZV-2NTFX, Long Barrel Narrow Tongue |
| UPC | 781810165997 |

Dimensions

| | |
|------------------------------------|----------|
| Dimension - B Length fraction | 1-5/8 in |
| Dimension - B Length inch | 1.62 in |
| Dimension - Bolt Hole Size inch | 0.39 in |
| Dimension - Bolt Size fraction | 3/8 |
| Dimension - Bolt Size inch | 0.38 |
| Dimension - Diameter Min Size inch | 1.84 in |
| Dimension - Hole Size fraction | 3/8 |
| Dimension - Hole Size inch | 0.41 |
| Dimension - Hole Size mm | 10.4 mm |
| Dimension - L Length Overall mm | 101 mm |
| Dimension - Length Overall inch | 3.96 in |
| Dimension - Length Side B inch | 3.96 in |
| Dimension - N inch | 0.41 in |
| Dimension - Outside Diameter inch | 0.77 in |
| Dimension - Pad Width inch | 0.94 in |
| Dimension - Strip Length inch | 1-11/16 |
| Dimension - Stud Size fraction | 3/8 |

Conductor Related

| | |
|--------------------------------------|--|
| Conductor - Copper DLO Size | 4/0 AWG |
| Conductor - Copper DLO Size Range | 4/0 AWG |
| Conductor - Copper Flex G Size | "4/0 AWG" |
| Conductor - Copper Flex G Size Range | 4/0 AWG |
| Conductor - Copper Flex H Size | "4/0 AWG" |
| Conductor - Copper Flex H Size Range | 4/0 AWG |
| Conductor - Copper Flex I Size | "4/0 AWG" |
| Conductor - Copper Flex I Size Range | 4/0 AWG |
| Conductor - Copper Flex K Size | "4/0 AWG" |
| Conductor - Copper Flex K Size Range | 4/0 AWG |
| Conductor - Copper Flex M Size | "4/0 AWG" |
| Conductor - Copper Str Compact Size | "4/0 AWG" |
| Conductor - Copper Str Navy Size | 200 |
| Conductor - Copper Str Size | "4/0 AWG" |
| Conductor - Copper Str Size Range | 4/0 AWG |
| Conductor - CopperWeld Str Size | 4/0 E AWG;4/0 EK AWG;4/0 F AWG;4/0 G AWG;4/0 V AWG |
| Conductor - Material | COPPER |
| Conductor Size | 4/0 AWG |
| Conductor Type | CODE/FLEX |
| Wire Size | 4/0 AWG |

Certifications and Compliance

| | |
|------------------------------------|--------------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------------------|----------|
| Dimension - Stud Size inch | 3/8 in |
| Dimension - Z inch | 0.43 in |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|-------------------|-------|
| Voltage - Maximum | 35000 |
| Voltage Rating | 35 kV |

Logistics

| | |
|-----------------------|-------|
| Carton Quantity | 50 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 11100 |

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Copper Flex Long Terminals Tooling and Installation Instructions](#)
- [Sales Drawings - 30003952](#)
- [Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAZV282NT38FX-SPEC-EN | REV 8/2023