



YAZV292NTCFX, Compression Terminal, 4/0 Flex Class I,K,M, 250 Code, 2-Hole, 1/2" Stud, Long Barrel

By Burndy
Catalog # [YAZV292NTCFX](#)

Copper Tubing Terminal, 2 Pad Holes, 4/0 Flex Class I,K,M, 250 Code, 16 Index, 1/2 IN Bolt.



Application

Wire Termination

General

| | |
|--------------------------------------|----------------------|
| Catalog Number | YAZV292NTCFX |
| Color Code | Yellow |
| Connector Type | LONG BARREL |
| Die Index | 16 |
| Feature - Barrel Style | Skived |
| Feature - Barrel Type | Long |
| Finish Type | Tin-Plated |
| Material | COPPER |
| Physical Attribute - Number of Holes | 2 |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Trade Name | HYLUG™ |
| Type | Long Barrel, Skive |
| UPC | 781810235188 |
| UPC 12 Digit | 7818102351888 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length fraction | 2 in |
| Dimension - B Length inch | 2.00 in |
| Dimension - Bolt Hole Size inch | 0.52 in |
| Dimension - Bolt Size fraction | 1/2 |
| Dimension - Bolt Size inch | 0.5 |
| Dimension - Hole Size fraction | 1/2 |
| Dimension - Hole Size inch | 0.56 |
| Dimension - Hole Size mm | 14 mm |
| Dimension - L Length Overall mm | 142 mm |
| Dimension - Length Overall inch | 5.59 in |
| Dimension - N inch | 0.62 in |
| Dimension - Outside Diameter inch | 0.80 in |
| Dimension - Pad Width inch | 1.18 in |
| Dimension - Strip Length inch | 2-1/16 |
| Dimension - Stud Size fraction | 1/2 |
| Dimension - Z (inch) | 0.65 in |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|-------------------|-------|
| Voltage - Maximum | 35000 |
| Voltage Rating | 35 kV |

Conductor Related

| | |
|--------------------------------------|-----------|
| Conductor - Copper DLO Size | 4/0 AWG |
| Conductor - Copper DLO Size Range | 4/0 AWG |
| Conductor - Copper Flex G Size | "4/0 AWG" |
| Conductor - Copper Flex G Size Range | 4/0 AWG |
| Conductor - Copper Flex H Size | "4/0 AWG" |
| Conductor - Copper Flex H Size Range | 4/0 AWG |
| Conductor - Copper Flex I Size | "4/0 AWG" |
| Conductor - Copper Flex I Size Range | 4/0 AWG |
| Conductor - Copper Flex K Size | "4/0 AWG" |
| Conductor - Copper Flex K Size Range | 4/0 AWG |
| Conductor - Copper Flex M Size | "4/0 AWG" |
| Conductor - Copper Flex M Size Range | 4/0 AWG |
| Conductor - Copper Str Compact Size | "4/0 AWG" |
| Conductor - Copper Str Navy Size | 200 |
| Conductor - Copper Str Size | "4/0 AWG" |
| Conductor - Copper Str Size Range | 250 kcmil |
| Conductor - Material | COPPER |
| Conductor Size | 250 KCMIL |
| Conductor Type | CODE/FLEX |
| Wire Size | 250 KCMIL |

Certifications And Compliance

| | |
|------------------------------------|--------------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 50 |
| Minimum Pack Quantity | 50 |
| Pallet Quantity | 6000 |

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE212404-01](#)
- [Specifications - YAZV292NTCFX](#)
- [Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YAZV292NTCFX-SPEC-EN | REV 8/2024