



## YAZV2C2NTCFX, Compression Terminal, 2 Flex G,H,I,K,M, DLO, 2 AWG, Cu, 2-Hole, 1/2" Stud, 1-3/4" Spacing, Long Barrel

By Burndy  
Catalog # [YAZV2C2NTCFX](#)



2 Flex G,H,I,K,M,DLO, 2 AWG CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Long Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Brown Color Code, 10 Die Index.

### Application

Wire Termination

### General

Catalog Number	YAZV2C2NTCFX
Color Code	Brown
Connector Type	LONG BARREL
Die Index	10
Feature - Barrel Style	<ul style="list-style-type: none"><li>• Chamfered</li><li>• Skived</li></ul>
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Long Barrel, Skive
UPC	781810228326
UPC 12 Digit	7818102283266

### Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	121 mm
Dimension - Length Overall inch	4.76 in
Dimension - Length Side B inch	4.76 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	1-7/16
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Z (inch)	0.65 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper DLO Size	2 AWG
Conductor - Copper DLO Size	2 AWG
Range	
Conductor - Copper Flex G Size	"2 AWG"
Conductor - Copper Flex G Size	2 AWG
Range	
Conductor - Copper Flex H Size	"2 AWG"
Conductor - Copper Flex H Size	2 AWG
Range	
Conductor - Copper Flex I Size	"2 AWG"
Conductor - Copper Flex I Size	2 AWG
Range	
Conductor - Copper Flex K Size	"2 AWG"
Conductor - Copper Flex K Size	2 AWG
Range	
Conductor - Copper Flex M Size	"2 AWG"
Conductor - Copper Flex M Size Range	2 AWG
Conductor - Copper Str Compact Size	"2 AWG"
Conductor - Copper Str Navy Size	60
Conductor - Copper Str Size	"2 AWG"
Conductor - Copper Str Size	2 AWG
Range	
Conductor - CopperWeld Str Size	2 A AWG;2 F AWG;2 G AWG;2 J AWG;2 K AWG;2 N AWG;2 P AWG
Conductor - CopperWeld Str Size Range	2 A AWG-2 P AWG
Conductor - Material	COPPER
Conductor Size	2 AWG
Conductor Type	CODE/FLEX
Wire Size	2 AWG

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	11600

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Copper Flex Long Terminals Tooling and Installation Instructions](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - SE..212273-15](#)  
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-YAZV2C2NTCFX-SPEC-EN | REV 8/2024