

Compression Terminal

By Burndy
Catalog # [YAZV4C2NT14E2FX](#)

4 Flex G,H,I,K,M,DLO, 4 AWG CU, Two Hole, 1/4 Stud Size, 3/4 Hole Spacing, Long Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Gray Color Code, 8 or 346 Die Index.



Application

Wire Termination

General

Color Code	Gray
Connector Type	LONG BARREL
Die Index	8
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810248966

Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - Diameter Min Size inch	1.40 in
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	75 mm
Dimension - Length Overall inch	2.95 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.38 in
Dimension - Pad Width inch	0.44 in
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size fraction	1/4
Dimension - Z inch	0.34 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	25000
-------------------	-------

Conductor Related

Conductor - Copper DLO Size	4 AWG
Conductor - Copper DLO Size Range	4 AWG
Conductor - Copper Flex G Size	"4 AWG"
Conductor - Copper Flex G Size Range	4 AWG
Conductor - Copper Flex H Size	"4 AWG"
Conductor - Copper Flex H Size Range	4 AWG
Conductor - Copper Flex I Size	"4 AWG"
Conductor - Copper Flex I Size Range	4 AWG
Conductor - Copper Flex K Size	"4 AWG"
Conductor - Copper Flex K Size Range	4 AWG
Conductor - Copper Flex M Size	"4 AWG"
Conductor - Copper Str Compact Size	"4 AWG"
Conductor - Copper Str Navy Size	40
Conductor - Copper Str Size	"4 AWG"
Conductor - Copper Str Size Range	4 AWG
Conductor - CopperWeld Str Size	4 A AWG;4 D AWG;4 N AWG;4 P AWG
Conductor - Material	COPPER
Conductor Size	4 AWG
Conductor Type	CODE/FLEX
Wire Size	4 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Voltage - Maximum 35000
Voltage Rating 35 kV

Carton Quantity 25
Minimum Pack Quantity 25

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Flex Long Terminals Tooling and Installation Instructions](#)
[Sales Drawings - 30003952](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAZV4C2NT14E2FX-SPEC-EN | REV 8/2023