



YAZV6C2TC10FX90SL, Compression Terminal, 6 61/24 DLO, 6 Code, 30 Navy, 2-Hole, #10 Stud, Slotted, Long Barrel, 90 Degree



By Burndy

Catalog # [YAZV6C2TC10FX90SL](#)

Copper Tubing Terminal, 6 (61/#24) DLO, #6 Code, 30 Navy, #10 Bolt, 7 or 374 Index.

Application

Wire Termination

General

Catalog Number	YAZV6C2TC10FX90SL
Color Code	Blue
Connector Type	LONG BARREL
Die Index	7
Feature - Barrel Style	<ul style="list-style-type: none">• Chamfered• Skived
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Skive
UPC	781810217412
UPC 12 Digit	7818102174122

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - Bolt Hole Size inch	0.20 in
Dimension - Bolt Size fraction	#8-#10
Dimension - Bolt Size inch	0.21
Dimension - Height inch	0.97 in
Dimension - Hole Size fraction	#10
Dimension - Hole Size inch	0.21
Dimension - Hole Size mm	5.3 mm
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.31 in
Dimension - Pad Width inch	0.48 in
Dimension - Strip Length inch	1-3/16
Dimension - Stud Size fraction	#10
Dimension - Stud Size inch	#10
Dimension - Z (inch)	0.28 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	6 AWG
Conductor - Copper DLO Size	6 AWG
Range	
Conductor - Copper Flex G Size	"6 AWG"
Conductor - Copper Flex G Size	6 AWG
Range	
Conductor - Copper Flex H Size	"6 AWG"
Conductor - Copper Flex H Size	6 AWG
Range	
Conductor - Copper Flex I Size	"6 AWG"
Conductor - Copper Flex I Size	6 AWG
Range	
Conductor - Copper Flex K Size	"6 AWG"
Conductor - Copper Flex K Size	6 AWG
Range	
Conductor - Copper Flex M	"6 AWG"
Size	
Conductor - Copper Flex M	6 AWG
Size Range	
Conductor - Copper Solid Size	6 AWG
Conductor - Copper Solid Size	6 Sol
Range	
Conductor - Copper Str	"6 AWG"
Compact Size	
Conductor - Copper Str Navy	30
Size	
Conductor - Copper Str Size	"6 AWG"
Conductor - Copper Str Size	6 AWG
Range	
Conductor - CopperWeld C	6 AWG
Solid Size	
Conductor - CopperWeld Solid	6 AWG
Size Range	
Conductor - CopperWeld Str	6 A AWG;6 C AWG;6 D AWG
Size	
Conductor - CopperWeld Str	6 A AWG-6 D AWG
Size Range	
Conductor - Material	COPPER
Conductor Size	6 AWG
Conductor Type	CODE/FLEX
Wire Size	6 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SE212012-01_C](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YAZV6C2TC10FX90SL-SPEC-EN | REV 8/2024