



# Uninsulated Flag-Type Ring Terminal For 4 AWG

By Burndy  
Catalog # [YBM4CL2](#)



Flag-Type Compression Ring Terminal; Accommodates: #4 AWG Flex Class I; #4 (105/24) DLO, #4 AWG Code; Stud: 3/8"; Die Index: 56

## General

Connector Type	Flag Ring Terminal
Construction Material - Main	Copper
Die Index	56
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Number of Holes	1
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	YBM
UPC	781810039847

## Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.59 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Length Overall inch	1.33 in
Dimension - N inch	0.36 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Pad Width inch	0.66 in
Dimension - Strip Length inch	5/8
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	90 Degree

## Conductor Related

Conductor - Copper DLO Size	4 (105/#24)
Conductor - Copper Flex I Size	4
Conductor - Copper Str Aircraft Size	AN 4
Conductor - Copper Str Size	4
Conductor - Copper Str Size Range	4 AWG
Conductor Size	4 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	76800

## Product Assets

[3D Models - YBM4CL2\\_MODEL-IGES](#)  
[3D Models - YBM4CL2\\_MODEL-PDF](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50094169](#)



A proud member of the Hubbell Family.

