



# Uninsulated Flag-Type Ring Terminal For 6 AWG

By Burndy  
Catalog # [YBM6CL9](#)



Uninsulated Flag-Type Ring Terminal For 6 AWG.

## General

Connector Type	Flag Ring Terminal
Die Index	55
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810026298

## Dimensions

Dimension - B Length fraction	9/16 in
Dimension - B Length inch	0.47 in
Dimension - Bolt Hole Size inch	0.2 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - Length Overall inch	1.09 in
Dimension - N inch	0.27 in
Dimension - Outside Diameter inch	0.37 in
Dimension - Pad Width inch	0.53 in
Dimension - Strip Length inch	1/2
Dimension - Stud Size inch	#8;#10
Dimension - Z inch	0.36 in
Physical Attribute - Tongue Angle	90 Degree

## Conductor Related

Conductor - Copper DLO Size	6 (61/#24)
Conductor - Copper Flex I Size	6
Conductor - Copper Str Aircraft Size	AN 6
Conductor - Copper Str Size	6
Conductor - Copper Str Size Range	6 AWG
Conductor Size	6 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	96000

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50094169](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YBM6CL9-SPEC-EN | REV 8/2023

