

YC25A25, Aluminum C-Shape Connector

By Burndy
Catalog # [YC25A25](#)



Range-taking, C-shaped AL compression tap, Run: Aluminum:
1/0- 2/0, ACSR: 1/0, Tap: Aluminum: 1/0- 2/0, ACSR: 1/0.

General

Catalog Number	YC25A25
Die Index	Q
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	CRIMPIT™
Type	YC-A, YC-U Series
UPC	781810123621
UPC 12 Digit	7818101236211

Dimensions

Dimension - Height inch	1.36 in
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.75 in

Conductor Related

Conductor - ACSR Str Run	1/0 Str
Conductor - ACSR Str Tap	1/0 Str
Conductor - AL Str Run	1/0 AWG;2/0 AWG
Conductor - AL Str Run Range	1/0 AWG - 2/0 AWG
Conductor - AL Str Tap	1/0 AWG;2/0 AWG
Conductor - AL Str Tap Range	1/0 AWG - 2/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	50
Pallet Quantity	14800

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_ycala](#)
- [Sales Drawings - 27166](#)