



YC26A26, Aluminum C-Shape Connector

By Burndy
Catalog # [YC26A26](#)



Range-taking, C-shaped AL compression tap, or dead-ending connector designed to eliminate the effects of cold flow, Prefilled with Penetrox.

Application

For Combinations Of Aluminum, ACSR, 6201, 5005, Compressed and Compact Conductors

General

Die Index	D
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YC-A, YC-U Series
UPC	781810124826
UPC 12 Digit	7818101248266

Dimensions

Dimension - Height inch	1.38 in
Dimension - L Length Overall mm	65 mm
Dimension - Length Overall inch	2.56 in

Conductor Related

Conductor - ACSR Str Run Range	1/0 AWG - 2/0 AWG
Conductor - ACSR Str Tap	2/0 Str
Conductor - AL Str Run	1/0 AWG;2/0 AWG
Conductor - AL Str Run Range	1/0 AWG - 2/0 AWG
Conductor - AL Str Tap	2/0 Str
Conductor - AL Str Tap Range	2/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	50
Pallet Quantity	7200

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 27166](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YC26A26-SPEC-EN | REV 8/2023