



YC26L12, Compression C-Tap, Run 2/0-#1 AWG, Tap #1-#12 AWG

By Burndy
Catalog # YC26L12



Copper Compression C Tap, Thin Wall, Run 2/0-#1 AWG, Tap #1-#12 AWG

Application

Wire Tap

General

Catalog Number	YC26L12
Color Code	Purple
Connector Type	C-TAP
Die Index	15
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Bright
Sub Brand	CRIMPIT
Temperature Rating	194
Trade Name	CRIMPIT™
Type	YC-L Series
UPC	781810040188
UPC 12 Digit	7818100401888

Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.69 in
Dimension - D inch	1.75 in
Dimension - Pad Width inch	0.43 in
Dimension - Strip Length inch	1-13/16

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Str Run	2/0 AWG-1 AWG
Conductor - Copper Str Run Range	2/0 AWG-1 AWG
Conductor - Copper Str Tap	1 AWG-12 AWG
Conductor - Copper Str Tap Range	1 AWG-12 AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG-12 AWG
Conductor Type	CODE

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	24000

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SC..208529-01](#)
[Specifications - YC26L12](#)



A Hubbell brand