



# YC2A6, Aluminum C-Shape Connector

By Burndy  
Catalog # [YC2A6](#)



Al Compression Tap(C-Shaped),#2 Sol./Str.Al, #4 - #2 AWG  
ACSR(Run), #6 Sol./Str. Al(Tap), 1.50" L.

## General

Die Index	C
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	CRIMPIT™
Type	YC-A, YC-U Series
UPC	781810122402
UPC 12 Digit	7818101224022

## Dimensions

Dimension - Height inch	1.00 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in

## Conductor Related

Conductor - ACSR Str Run Range	4 AWG - 2 AWG
Conductor - AL Str Run Range	2 Sol. - 2 Str
Conductor - AL Str Tap Range	6 Sol. - 6 Str.

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 27166](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YC2A6-SPEC-EN | REV 8/2023