




YC2C2, Copper C-Shape Connector

By Burndy
Catalog # [YC2C2](#)

CU Compression C Shape Compression Connector, 600 Volts to 35 Kv, 2 Sol. - 2 Str. (Run & Tap).



Application

For Range Of Copper And Making Tap Or Parallel Copper Connections

General

Die Index	C
EU RoHS Indicator	Yes
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YC-C Series
UPC	781810111505
UPC 12 Digit	7818101115055

Dimensions

Dimension - Height inch	1.05 in
Dimension - L Length Overall mm	17 mm
Dimension - Length Overall inch	0.67 in

Conductor Related

Conductor - Copper Solid Run	2 AWG
Conductor - Copper Solid Run Range	2 AWG
Conductor - Copper Solid Tap	2 AWG
Conductor - Copper Solid Tap Range	2 AWG
Conductor - Copper Str Run	2 AWG
Conductor - Copper Str Run Range	2 Sol. - 2 Str
Conductor - Copper Str Tap	2 AWG
Conductor - Copper Str Tap Range	2 Sol. - 2 Str
Conductor Type	Cu C Sol-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">UL 486AUL486B
Standards - Industry Standards Met	UL 486A;UL486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	23200

Product Assets

[3D Models - YC2C2_MODEL-PDF](#)
[3D Models - YC2C2_MODEL-IGES](#)
[3D Models - YC2C2_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YCC_Lineart](#)
[Sales Drawings - SE..090670-01](#)



A proud member of the Hubbell Family.

