

YC2L12, Cu Compression C-Tap, Thin Wall

By Burndy
Catalog # YC2L12



Copper Compression C Tap, Thin Wall, 4 AWG (Run), 4 AWG (Tap).

Application

Wire Tap

General

Catalog Number	YC2L12
Color Code	Pink
Connector Type	C-TAP
Die Index	12
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Bright
Sub Brand	CRIMPIT
Temperature Rating	194
Trade Name	CRIMPIT™
Type	YC-L Series
UPC	781810040157
UPC 12 Digit	7818100401577

Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - D inch	1.18 in
Dimension - Pad Width inch	0.36 in
Dimension - Strip Length inch	1-3/16

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Str Run	2 AWG-4 AWG
Conductor - Copper Str Run Range	2 AWG-4 AWG
Conductor - Copper Str Tap	4 AWG-12 AWG
Conductor - Copper Str Tap Range	4 AWG-12 AWG
Conductor - Material	COPPER
Conductor Size	2 AWG-12 AWG
Conductor Type	CODE

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	57600

Product Assets

- [3D Models - YC2L12_MODEL-IGES](#)
- [3D Models - YC2L12_MODEL-PDF](#)
- [3D Models - YC2L12_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SC..208529-01](#)
- [Specifications - YC2L12](#)



A Hubbell brand