

# YC2L12TN, Compression C-Tap, Main #2-#4 AWG, Tap #4-#12 AWG, Tin Plated

By Burndy  
Catalog # YC2L12TN



Cu Thin Wall C-Tap, Compression, #2 - #4 AWG(Main), #4 - #12 AWG(Tap), 600 V, Tin Plated.

## Application

Wire Tap

## General

Catalog Number	YC2L12TN
Color Code	Yellow
Connector Type	C-TAP
Die Index	12
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	CRIMPIT™
Type	YC-L Series
UPC	781810040225
UPC 12 Digit	7818100402255

## Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - D inch	1.18 in
Dimension - Pad Width inch	0.36 in
Dimension - Strip Length inch	1-3/16

## Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

## Conductor Related

Conductor - Copper Str Run	2 AWG-4 AWG
Conductor - Copper Str Run Range	2 AWG-4 AWG
Conductor - Copper Str Tap	4 AWG-12 AWG
Conductor - Copper Str Tap Range	4 AWG-12 AWG
Conductor - Material	COPPER
Conductor Size	2 AWG-12 AWG
Conductor Type	CODE

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Carton Quantity	400
Minimum Pack Quantity	400
Pallet Quantity	48000

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - SC..208529-01](#)  
[Specifications - YC2L12TN](#)