



YC4A4, Aluminum C-Shape Connector

By Burndy
Catalog # YC4A4



Al Compression Tap(C-Shaped), 6 Sol. - 4 Str. Al, #6
ACSR(Run), 4 Sol. - 4 Str. Al, #6 ACSR(Tap).

General

Die Index	BG
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	CRIMPIT™
Type	YC-A, YC-U Series
UPC	781810122709
UPC 12 Digit	7818101227099

Dimensions

Dimension - Height inch	075 in
Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.25 in

Conductor Related

Conductor - AAAC 5005 Tap	30.58 (7) kcmil
Conductor - AAAC 5005 Tap Range	30.58 (7) kcmil
Conductor - AAAC 6201 Tap	30.58 (7) kcmil
Conductor - ACSR Str Run	6
Conductor - ACSR Str Tap	6
Conductor - AL Str Run	6 AWG;4 AWG
Conductor - AL Str Run Range	6 Sol. - 4 Str
Conductor - AL Str Tap Range	4 Sol. - 4 Str.

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	29600

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 27166](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YC4A4-SPEC-EN | REV 8/2023