


YC4C4, Copper C-Shape Connector

By Burndy
Catalog # YC4C4

CU Compression C Shape Compression Connector, 600 Volts to 35 Kv, 6 Sol. - 4 Str. (Run & Tap).



Application

For Range Of Copper And Making Tap Or Parallel Copper Connections

General

Catalog Number	YC4C4
Die Index	BG or 5/8
EU RoHS Indicator	Yes
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YC-C Series
UPC	781810113509
UPC 12 Digit	7818101135099

Dimensions

Dimension - Height inch	0.81 in
Dimension - L Length Overall mm	14 mm
Dimension - Length Overall inch	0.57 in

Conductor Related

Conductor - Copper Solid Run Range	6 Sol. - 4 Str.
Conductor - Copper Solid Tap Range	6 Sol. - 4 Str.
Conductor - Copper Str Run Range	6 Sol. - 4 Str.
Conductor - Copper Str Tap	4 AWG
Conductor Type	Cu C Sol-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> UL 486A UL486B
Standards - Industry Standards Met	UL 486A;UL486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	57600

Product Assets

- [3D Models - YC4C4_MODEL-STEP](#)
- [3D Models - YC4C4_MODEL-IGES](#)
- [3D Models - YC4C4_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YCC_Lineart](#)
- [Sales Drawings - SE..090670-01](#)