




YC4C6, Copper C-Shape Connector

By Burndy
Catalog # [YC4C6](#)



CU Compression C Shape Compression Connector, 600 Volts to 35 Kv, Run: 6 Sol. - 4 Str., Tap: 6 Sol. - 6 Str.

Application

For Making Tap Or Parallel Copper Connections

General

Die Index	BG or 5/8
EU RoHS Indicator	Yes
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YC-C Series
UPC	781810113752
UPC 12 Digit	7818101137522

Dimensions

Dimension - Height inch	0.76 in
Dimension - L Length Overall mm	14 mm
Dimension - Length Overall inch	0.57 in

Conductor Related

Conductor - Copper Solid Run Range	6 Sol. - 4 Str.
Conductor - Copper Solid Tap	6 AWG
Conductor - Copper Str Run Range	6 Sol. - 4 Str.
Conductor - Copper Str Tap	6 AWG
Conductor Type	Cu C Sol-Size

Certifications and Compliance

Certification - CSA Approved	No
Industry Standard(s)	<ul style="list-style-type: none">• UL 486A• UL486B
Standards - Industry Standards Met	UL 486A;UL486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	57600

Product Assets

[3D Models - YC4C6_MODEL-PDF](#)
[3D Models - YC4C6_MODEL-STEP](#)
[3D Models - YC4C6_MODEL-IGES](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SE..090670-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YC4C6-SPEC-EN | REV 8/2023