

YC4C8, Copper C-Shape Connector

By Burndy
Catalog # [YC4C8](#)



CU Compression C Shape Compression Connector, 600 Volts to 35 Kv, Run: 6 Sol. - 4 Str., Tap: 8 Sol. - 8 Str.

Features

- Range-taking connector lowering inventory requirements
- Compact size, easy to tape and insulate connection
- High conductivity wrought copper provides low resistance and excellent electrical conductivity

Application

For Making Tap Or Parallel Copper Connections

General

Catalog Number	YC4C8
Die Index	BG or 5/8
EU RoHS Indicator	Yes
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YC-C Series
UPC	781810114254
UPC 14 Digit GTIN	00781810114254

Dimensions

Dimension - Height inch	0.73 in
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	16 mm
Dimension - Length Overall inch	0.62 in

Conductor Related

Conductor - Copper Solid Run Range	6 Sol. - 4 Str.
Conductor - Copper Solid Tap	8 AWG

Conductor - Copper Str Run Range	6 Sol. - 4 Str.
Conductor - Copper Str Tap	8 AWG
Conductor Type	Cu C Sol-Size

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">• UL 486A• UL486B
Standards - Industry Standards Met	UL 486A;UL486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	57600

Product Assets

[3D Models - YC4C8_MODEL-PDF](#)
[3D Models - YC4C8_MODEL-STEP](#)
[3D Models - YC4C8_MODEL-IGES](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YCC_Lineart](#)
[Sales Drawings - SE..090670-01](#)
[Specifications - YC4C8](#)