

Compression C-Tap

By Burndy
Catalog # YC6L12TN

Cu Thin Wall C-Tap, Compression, #6 - #8 AWG(Main), #8 - #12 AWG(Tap), 600 V, Tin Plated.



Application

Wire Tap

General

Color Code	Gray
Connector Type	C-TAP
Die Index	8
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	CRIMPIT™
Type	YC-L Series
UPC	781810243350
UPC 12 Digit	7818102433500

Dimensions

Dimension - B Length fraction	5/16 in
Dimension - B Length inch	0.33 in
Dimension - D inch	0.60 in
Dimension - Pad Width inch	0.25 in
Dimension - Strip Length inch	5/8

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Str Run	6 AWG-8 AWG
Conductor - Copper Str Run Range	6 AWG-8 AWG
Conductor - Copper Str Tap	8 AWG-12 AWG
Conductor - Copper Str Tap Range	8 AWG-12 AWG
Conductor - Material	COPPER
Conductor Size	6 AWG-12 AWG
Conductor Type	CODE

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	200
Minimum Pack Quantity	1
Pallet Quantity	59200

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SC..208529-01](#)