

YC8L12TN, Compression C-Tap, Main #8-#10 AWG, Tap #10-#12 AWG, Tin Plated

By Burndy
Catalog # YC8L12TN



Cu Thin Wall C-Tap, Compression, #8 - #10 AWG(Main), #10 - #12 AWG(Tap), 600 V, Tin Plated.

Application

Wire Tap

General

Catalog Number	YC8L12TN
Color Code	Blue
Connector Type	C-TAP
Die Index	7
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	CRIMPIT™
Type	YC-L Series
UPC	781810243367
UPC 12 Digit	7818102433677

Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.25 in
Dimension - D inch	0.60 in
Dimension - Pad Width inch	0.21 in
Dimension - Strip Length inch	5/8

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Str Run	8 AWG-10 AWG
Conductor - Copper Str Run Range	8 AWG-10 AWG
Conductor - Copper Str Tap	12 AWG-10 AWG
Conductor - Copper Str Tap Range	12 AWG-10 AWG
Conductor - Material	COPPER
Conductor Size	8 AWG-12 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	2000
Minimum Pack Quantity	2000
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SC..208529-01](#)
[Specifications - YC8L12TN](#)