

# YCA252NDT, Copper compression terminal, 1/0 Stranded, 2-hole, 1/2" Stud, 1-3/4" Spacing, Dip Tin Plate

By Burndy  
Catalog # [YCA252NDT](#)



Cu Wire lug, 1/0 str, .56"stud, 5.34"L.

## General

Catalog Number	YCA252NDT
Connector Type	Terminal
Die Index	165
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	781810081082
UPC 12 Digit	7818100810822

## Dimensions

Dimension - B Length fraction	1-4/7 in
Dimension - B Length inch	1.57 in
Dimension - D inch	3.00 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	136 mm
Dimension - Length Overall inch	5.34 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	0.91 in
Dimension - Strip Length inch	1 5/8
Dimension - Z (inch)	0.62 in
Physical Attribute - Tongue Angle	Straight

## Conductor Related

Conductor - Copper Str Size	1/0
Conductor - Copper Str Size Range	1/0

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	7400

## Product Assets

- [3D Models - YCA252NDT\\_MODEL-STEP](#)
- [3D Models - YCA252NDT\\_MODEL-PDF](#)
- [3D Models - YCA252NDT\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD..029071-01](#)
- [Specifications - YCA252NDT](#)