



YCA252NDTS

By Burndy
Catalog # [YCA252NDTS](#)



Cu Compression terminal Designed for terminating Cu Conductors to switch pads, 1/0 Str., 1/2 IN Stud, 2 Pad holes, Sealed oil tight and tin plated.

General

Connector Type	Terminal
Die Index	165
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	781810085080

Dimensions

Dimension - B Length fraction	1-4/7 in
Dimension - B Length inch	1.57 in
Dimension - D inch	2.67 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	136 mm
Dimension - Length Overall inch	5.34 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	0.91 in
Dimension - Z inch	0.30 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size 1/0

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	7400

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd029071-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YCA252NDTS-SPEC-EN | REV 8/2023