

YCA322N

By Burndy
Catalog # [YCA322N](#)



Copper compression lug designed for terminating copper conductors to switch pads and other substation switch yard apparatus, 6.72 IN L.

General

Connector Type	Terminal
Die Index	209
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	781810014738

Dimensions

Dimension - B Length inch	2.78 in
Dimension - D inch	3.00 in
Dimension - Hole Size fraction	14/25 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	171 mm
Dimension - Length Overall inch	6.72 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.24 in
Dimension - Pad Width inch	1.67 in
Dimension - Strip Length inch	2 5/8
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.62 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	400 kcmil
Conductor - Copper Str Size Range	400 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	15
Minimum Pack Quantity	1
Pallet Quantity	1110

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - SD..029071-01](#)