



YCA451A4N, Al compression terminal, 4-Hole, 1/2" Stud, 1-3/4" Spacing, 113 ACSR, 1272 kcmil AL

By Burndy
Catalog # [YCA451A4N](#)



Aluminum Terminal, 4 Pad Holes, 1113 (54-19) kcmil ACSR, 1272 (61) kcmil AL., 422 Index

General

| | |
|--|---------------|
| Connector Type | Terminal |
| Die Index | 422 |
| Material | Aluminum |
| Physical Attribute - Pad Configuration | 4 Hole NEMA |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | Y |
| Trade Name | HYLUG™ |
| UPC | 781810016725 |
| UPC 12 Digit | 7818100167255 |

Dimensions

| | |
|--|----------|
| Dimension - B Length inch | 4.92 in |
| Dimension - Bolt Hole Size inch | 0.56 in |
| Dimension - E Spacing between Holes fraction | 1-3/4 in |
| Dimension - L Length Overall mm | 259 mm |
| Dimension - Length Overall inch | 10.19 in |
| Dimension - Pad Width inch | 3 in |

Conductor Related

| | |
|---------------------------------|--------------------|
| Conductor - ACSR Str Size | 1113 (54-19) kcmil |
| Conductor - ACSR Str Size Range | 1113 (54/19) kcmil |
| Conductor - AL Str Size | 1272 (61) kcmil |

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|-----|
| Carton Quantity | 8 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 720 |

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YCA_LineArt](#)
[Sales Drawings - SD..029515-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YCA451A4N-SPEC-EN | REV 5/2024