



YCAK25R4n, Al compression lug, 4-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YCAK25R4N](#)

Aluminum compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus.



General

Die Index	243;BG
Material	Aluminum
Physical Attribute - Pad Configuration	4 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810081433
UPC 12 Digit	7818100814333

Dimensions

Dimension - B Length inch	2.62 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	174 mm
Dimension - Length Overall inch	6.86 in
Dimension - Pad Width inch	3 in

Conductor Related

Conductor - ACSR Str Size	1/0 (6/1) AWG
Conductor - ACSR Str Size Range	1/0 (6/1) AWG
Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..029515-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YCAK25R4N-SPEC-EN | REV 5/2024