



YCAK26R4N, Al terminal, 4-Hole, 1/2" Stud, 1-3/4" Spacing, 2/0 AWG ACSR, AL

By Burndy
Catalog # [YCAK26R4N](#)



Aluminum Terminal, 4 Pad Holes, 2/0 (6-1) AWG ACSR, 2/0 (7,19) AWG Al., 245 Index.

General

Catalog Number	YCAK26R4N
Die Index	245
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810016930
UPC 12 Digit	7818100169300

Dimensions

Dimension - B Length inch	2.60 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	174 mm
Dimension - Length Overall inch	6.86 in
Dimension - Pad Width inch	3 in

Conductor Related

Conductor - ACSR Str Size	2/0 AWG
Conductor - AL Str Size	2/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	3
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YCAK26R4N_LineArt](#)
- [Sales Drawings - SD..029515-01](#)
- [Specifications - YCAK26R4N](#)