



YCAK27R2G2

By Burndy
Catalog # [YCAK27R2G2](#)

Cast Aluminum Compression Terminal, 2 Pad Holes, 3/0 AWG (7,19) Cu & Al, 3/0 (6-1) AWG , 317 or 705 Index.



General

Die Index	317;705
Material	Aluminum, Cast
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810016855
UPC 12 Digit	7818100168555

Dimensions

Dimension - B Length inch	3 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	184 mm
Dimension - Length Overall inch	7.25 in

Conductor Related

Conductor - ACSR Str Size	3/0 AWG
Conductor - AL Str Size	3/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	3
-----------------------	---

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD062358-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YCAK27R2G2-SPEC-EN | REV 8/2023