



YCAK28A2G1, Aluminum terminal, 4/0 Str Cu/Al

By Burndy
Catalog # [YCAK28A2G1](#)

Aluminum Terminal, 4/0 Str. Cu,Al Conc.& Compact, 317 or 705 Index.



General

Catalog Number	YCAK28A2G1
Die Index	317;705
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810810248
UPC 12 Digit	7818108102488

Dimensions

Dimension - B Length fraction	5-5/8 in
Dimension - B Length inch	1.56 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - D inch	3 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	143 mm
Dimension - Length Overall inch	5.63 in
Dimension - Pad Width inch	1.25 in

Conductor Related

Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YCAK-A_LineArt](#)
- [Sales Drawings - SD64095-01_A](#)
- [Specifications - YCAK28A2G1](#)