



# YCAK33R4N, Al compression terminal, 4-Hole, 1/2" Stud, 1-3/4" Spacing, 336.4 kcmil ACSR, 397.5 kcmil Al



By Burndy  
Catalog # [YCAK33R4N](#)

Al Compression terminal, 336.4 Kcmil ACSR(26-7, 30-7) str 397.5 Kcmil Al(19)Str, .56"stud, 7.34"L, , 316 index.

## Application

For ACSR/6201/5005 (Compressed/Compact), Aluminum

## General

Catalog Number	YCAK33R4N
Die Index	316
EU RoHS Indicator	Yes
Material	Aluminum
Physical Attribute - Pad Configuration	4 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS
Trade Name	HYLUG™
Type	YCAK-R-N, Terminal
UPC	781810810231
UPC 12 Digit	7818108102311

## Dimensions

Dimension - B Length inch	3.05 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	187 mm
Dimension - Length Overall inch	7.34 in
Dimension - Pad Width inch	3 in

## Conductor Related

Conductor - ACSR Str Size	336.4 (26-7) kcmil;336.4 (30-7) kcmil
Conductor - ACSR Str Size Range	336.4 (26-7) kcmil;336.4 (30-7) kcmil
Conductor - AL Str Size	397.5 kcmil
Conductor - AL Str Size Range	397.5 kcmil

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Minimum Pack Quantity	10
-----------------------	----

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YCAK26R4N\\_LineArt](#)
- [Sales Drawings - SD..029515-01](#)
- [Specifications - YCAK33R4N](#)