



YCAK34A2G3

By Burndy
Catalog # [YCAK34A2G3](#)

Al Compression terminal, 500 kcmil 500 kcmil COMP, .56"stud, 6.55"L.



Application

For Copper, Aluminum Concentric And Compact

General

Die Index	608;786
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum
Physical Attribute - Pad Configuration	2 Hole NEMA
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS
Type	YCAK-A, Terminal
UPC	781810810309
UPC 12 Digit	7818108103099

Dimensions

Dimension - B Length fraction	6-1/2 in
Dimension - B Length inch	2.19 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	165 mm
Dimension - Length Overall inch	6.55 in
Dimension - Pad Width inch	1.50 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - AL Str Size	500 kcmil
Conductor - AL Str Size Range	500 kcmil
Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD64095-01_A](#)



A proud member of the Hubbell Family.