



YCAK45R4N, Al Compression Terminal, 4-Hole, 1/2" Stud, 1-3/4" Spacing

By Burndy
Catalog # [YCAK45R4N](#)



Aluminum Compression Terminal, 795 (26-7, 54-7) ACSR 900(61, 91),954(37, 61),1000(61) Al, 1/2" Stud.

Application

For AAC(STR,Compressed,compact), ACSR AND AAAC

General

Catalog Number	YCAK45R4N
Die Index	352
EU RoHS Indicator	Yes
Material	Aluminum
Physical Attribute - Pad Configuration	4 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	COMPRESSION TERMINAL
Type	YCAK-R-N
UPC	781810016794
UPC 12 Digit	7818100167944

Dimensions

Dimension - B Length inch	5.25 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	254 mm
Dimension - Length Overall inch	9.64 in
Dimension - Pad Width inch	4.00 in

Conductor Related

Conductor - ACSR Str Size	795 kcmil (54-7 STR)
Conductor - AL Str Size Range	900 kcmil (61,91 STR), 954 kcmil (37,61 STR),1000 kcmil (61 STR)

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - YCAK45R4N_MODEL-PDF](#)
- [3D Models - YCAK45R4N_MODEL-IGES](#)
- [3D Models - YCAK45R4N_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YCAK391A4N_LineArt](#)
- [Sales Drawings - SD..029515-01](#)
- [Specifications - YCAK45R4N](#)