



YCB26AU2G1

By Burndy
Catalog # YCB26AU2G1

Aluminum Cable CRIMPIT™, ACSR: 3 (6-1) AWG-1/0 (6-1) AWG, AL or CU: 2 AWG-2/0 AWG.



General

Die Index	O
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	CRIMPIT™
Type	Stirrups
UPC	781810014059
UPC 12 Digit	7818100140599

Dimensions

Dimension - F Width Center to Center inch	4.00 in
Dimension - Height inch	1.30 in
Dimension - L Length Overall mm	63 mm
Dimension - Length Overall inch	2.50 in

Conductor Related

Conductor - ACSR Str Size Range	3 (6-1) AWG-1/0 (6-1) AWG
Conductor - AL Str Size Range	2 AWG-2/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - YCB26AU2G1_MODEL-STEP](#)
[3D Models - YCB26AU2G1_MODEL-IGES](#)
[3D Models - YCB26AU2G1_MODEL-PDF](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SC..076872-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YCB26AU2G1-SPEC-EN | REV 8/2023