



YCB28U2G1

By Burndy
Catalog # [YCB28U2G1](#)

Combines figure 6-shaped aluminum CRIMPIT tap connector with tin-plated copper bail. Can be gripped in jaw and slid over line for easy installation.



Application

For Aluminum, ACSR, 6201, 5005, Compressed And Compact Conductors

General

Die Index	D3
EU RoHS Indicator	Yes
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	COMPRESSION TAP CONNECTOR, CABELOK CRIMPIT
Trade Name	CRIMPIT™
Type	Stirrups
UPC	781810014073
UPC 12 Digit	7818100140733

Dimensions

Dimension - Bail Size	0.258 in
Dimension - D inch	4.25 in
Dimension - F Width Center to Center inch	4.00 in
Dimension - Height inch	1.70 in
Dimension - L Length Overall mm	68 mm
Dimension - Length Overall inch	2.69 in
Dimension - Width inch	0.97 in
Dimension - Width mm	25 mm

Conductor Related

Conductor - ACSR Str Size	3/0 (6-1) AWG; 4/0 (6-1) AWG
Conductor - ACSR Str Size Range	3/0 (6-1) AWG-4/0 (6-1) AWG
Conductor - AL Str Size	4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor Type	<ul style="list-style-type: none">• ACSR Str-Size• AL Str-Size• CU Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	3600

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SC..076872-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YCB28U2G1-SPEC-EN | REV 8/2023