



# YCB321R, Aluminum Stirrup Connector, 336.4-350 kcmil Aluminum, ACSR: 300(26/7) kcmil, 336 (26/7, 26/7) 336.4 (18/1)



By Burndy  
Catalog # YCB321R

Stirrup Connector, Aluminum: 336.4 kcmil-350 kcmil, ACSR: 300(26/7) kcmil, 336.4(18/1) kcmil.

## General

Catalog Number	YCB321R
Die Index	M
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Type	Stirrups
UPC	781810153017
UPC 12 Digit	7818101530177

## Dimensions

Dimension - Bail Size	0.324 in
Dimension - D inch	3.50 in
Dimension - F Width Center to Center inch	3.50 in
Dimension - Height inch	5.39 in
Dimension - L Length Overall mm	324 mm
Dimension - Length Overall inch	12.75 in
Dimension - Width inch	1.31 in
Dimension - Width mm	33 mm

## Conductor Related

Conductor - ACSR Str Size	300.0 (26/7) Ostrich kcmil; 336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Size Range	300.0 (26/7) Ostrich kcmil-336.4 (18/1) Merlin kcmil
Conductor - AL Str Size	336.4 kcmil; 350 kcmil
Conductor - AL Str Size Range	336.4 kcmil - 350 Kcmil

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YCBR\\_Lineart](#)
- [Sales Drawings - 2979](#)
- [Specifications - YCB321R](#)