



# YCB33R, Aluminum Stirrup Connector, 397.5-400 kcmil Aluminum, ACSR: 336 (26/7, 30/7) 397.5 (18/1)



By Burndy  
Catalog # YCB33R

Stirrup Connector, Aluminum: 397.5 kcmil-400 kcmil,  
ACSR: 336.4(26/7) kcmil, 336.4(30/7) kcmil, 397.5(18/1) kcmil.

## General

Catalog Number	YCB33R
Die Index	M
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Type	Stirrups
UPC	781810152768
UPC 12 Digit	7818101527688

## Dimensions

Dimension - Bail Size	0.324 in
Dimension - D inch	3.50 in
Dimension - F Width Center to Center inch	3.50 in
Dimension - Height inch	5.39 in
Dimension - L Length Overall mm	324 mm
Dimension - Length Overall inch	12.75 in
Dimension - Width inch	1.31 in
Dimension - Width mm	33 mm

## Conductor Related

Conductor - ACSR Str Size	336.4 (26/7) Linnet kcmil; 336.4 (30/7) Oriole kcmil; 397.5 (18/1) Chickadee kcmil
Conductor - ACSR Str Size Range	336.4 (26/7) Linnet kcmil-397.5 (18/1) Chickadee kcmil
Conductor - AL Str Size	397 kcmil; 400 kcmil
Conductor - AL Str Size Range	397 kcmil - 400 kcmil

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Minimum Pack Quantity	6
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YCBB\\_Lineart](#)
- [Sales Drawings - 2979](#)
- [Specifications - YCB33R](#)