

YCB35R

By Burndy
Catalog # YCB35R

Stirrup Connector, Aluminum: 477 kcmil-500 kcmil,
ACSR: 397.5(30/7) kcmil-397.5(26/7) kcmil.



General

Die Index	M
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Type	Stirrups
UPC	781810152782
UPC 12 Digit	7818101527822

Dimensions

Dimension - Bail Size	0.324 in
Dimension - D inch	3.50 in
Dimension - F Width Center to Center inch	3.50 in
Dimension - Height inch	5.39 in
Dimension - L Length Overall mm	324 mm
Dimension - Length Overall inch	12.75 in
Dimension - Width inch	1.31 in
Dimension - Width mm	33 mm

Conductor Related

Conductor - ACSR Str Size	397.5 (26/7) Ibis kcmil; 397.5 (30/7) Larkspur kcmil
Conductor - ACSR Str Size Range	397.5 (26/7) Ibis kcmil-397.5 (30/7) Larkspur kcmil
Conductor - AL Str Size	477 kcmil; 500 kcmil
Conductor - AL Str Size Range	477 kcmil-500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	6
-----------------------	---

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 2979](#)