



## YCB4U1

By Burndy  
Catalog # YCB4U1

CRIMPIT™ HOT TAP, 4 (6-1) AWG, 4(7-1) AWG, ACSR: 4 AWG  
Cu or Al.



### General

Die Index	D
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Trade Name	CRIMPIT™
Type	Stirrups
UPC	781810151655
UPC 12 Digit	7818101516555

### Dimensions

Dimension - Bail Size	0.258 in
Dimension - D inch	4.25 in
Dimension - F Width Center to Center inch	4.00 in
Dimension - Height inch	1.47 in
Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.81 in

### Conductor Related

Conductor - AAAC 6201 Size	48.69 (7) kcmil
Conductor - ACSR Cmpt Size	4 AWG
Conductor - ACSR Str Size	4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Size Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG
Conductor - AL Str Size	4 AWG
Conductor - AL Str Size Range	4 AWG
Conductor - Copper Str Size	4 AWG
Conductor Type	<ul style="list-style-type: none"><li>• ACSR Str-Size</li><li>• AL Str-Size</li><li>• CU Str-Size</li></ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	25
Minimum Pack Quantity	2000
Pallet Quantity	3600

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SA..445376-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YCB4U1-SPEC-EN | REV 8/2023