

# Compression C-Tap

By Burndy  
Catalog # [YCHC29TC29](#)



Copper Compression C Tap, 250 kcmil- 2 AWG (Main), 250 kcmil- 2 AWG (Tap), Tin Plated.

## Application

Wire Tap

## General

Color Code	Orange
Connector Type	C-TAP
Die Index	997
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YCHC Series
UPC	781810013717
UPC 12 Digit	7818100137177

## Dimensions

Dimension - Height inch	2.12 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.94 in
Dimension - Strip Length inch	1 in
Dimension - Width inch	0.98 in

## Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

## Conductor Related

Conductor - Copper Flex I Run Range	2 AWG-4/0 AWG
Conductor - Copper Flex I Tap Range	2 AWG-4/0 AWG
Conductor - Copper Flex K Run Range	2 AWG-4/0 AWG
Conductor - Copper Flex K Tap Range	2 AWG-4/0 AWG
Conductor - Copper Flex M Run Range	2 AWG-4/0 AWG
Conductor - Copper Flex M Tap Range	2 AWG-4/0 AWG
Conductor - Copper Str Run Range	250 KCMIL-2 AWG
Conductor - Copper Str Run Range	250 KCMIL-2 AWG
Conductor - Copper Str Tap Range	250 KCMIL-2 AWG
Conductor - Copper Str Tap Range	250 KCMIL-2 AWG
Conductor - Material	COPPER
Conductor Size	250 KCMIL-250 KCMIL
Conductor Type	CODE/FLEX

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	24
Minimum Pack Quantity	1
Pallet Quantity	9408

## Product Assets

[3D Models - YCHC29TC29\\_MODEL-IGES](#)  
[3D Models - YCHC29TC29\\_MODEL-STEP](#)  
[3D Models - YCHC29TC29\\_MODEL-PDF](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD..206624-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YCHC29TC29-SPEC-EN | REV 8/2023