



YCHC34TC29, Cu Compression C Tap, 500 kcmil-4/0 AWG Run, 250 kcmil-2 AWG Tap 1, 2-6 AWG Tap 2

By Burndy
Catalog # [YCHC34TC29](#)



Copper Compression C Tap, 500 kcmil-4/0 AWG (Main), 250 kcmil-2 AWG (Tap 1), 2-6 AWG (Tap 2), Tin Plated.

Application

Wire Tap

General

Color Code	Brown
Connector Type	C-TAP
Die Index	1104
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YCHC Series
UPC	781810013762
UPC 12 Digit	7818100137622

Dimensions

Dimension - Height inch	2.45 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in
Dimension - Strip Length inch	1 in
Dimension - Width inch	1.26 in

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Flex I Run	4/0 AWG-350 kcmil
Conductor - Copper Flex I Tap	2 AWG-4/0 AWG
Conductor - Copper Flex K Run Range	4/0 AWG-350 kcmil
Conductor - Copper Flex K Tap Range	2 AWG-4/0 AWG
Conductor - Copper Flex M Run Range	4/0 AWG-350 kcmil
Conductor - Copper Flex M Tap Range	2 AWG-4/0 AWG
Conductor - Copper Str Run	500 KCMIL-4/0 AWG
Conductor - Copper Str Run Range	500 KCMIL-4/0 AWG
Conductor - Copper Str Tap	250 KCMIL-2 AWG
Conductor - Copper Str Tap Range	250 KCMIL-2 AWG
Conductor - Material	COPPER
Conductor Size	500 KCMIL-250 KCMIL
Conductor Type	CODE/FLEX

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	7400

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..206624-01](#)



A proud member of the Hubbell Family.