

# YCHC34TC34, Cu Compression C Tap, 500 kcmil-4/0 AWG Run and Tap



By Burndy  
Catalog # [YCHC34TC34](#)

Copper Compression C Tap, 500 kcmil-4/0 AWG (Main), 500 kcmil-4/0 AWG (Tap), Tin Plated.

## Application

Wire Tap

## General

Catalog Number	YCHC34TC34
Color Code	Brown
Connector Type	C-TAP
Die Index	1104
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YCHC Series
UPC	781810013724
UPC 12 Digit	7818100137244

## Dimensions

Dimension - Height inch	2.97 in
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1.00 in
Dimension - Strip Length inch	1-1/4
Dimension - Width inch	1.38 in

## Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

## Conductor Related

Conductor - Copper Flex I Run Range	4/0 AWG-350 kcmil
Conductor - Copper Flex I Tap Range	4/0 AWG-350 kcmil
Conductor - Copper Flex K Run Range	4/0 AWG-350 kcmil
Conductor - Copper Flex K Tap Range	4/0 AWG-350 kcmil
Conductor - Copper Flex M Run Range	4/0 AWG-350 kcmil
Conductor - Copper Flex M Tap Range	4/0 AWG-350 kcmil
Conductor - Copper Str Run Range	500 KCMIL-4/0 AWG
Conductor - Copper Str Tap Range	500 KCMIL-4/0 AWG
Conductor - Material	COPPER
Conductor Size	500 KCMIL-500 KCMIL
Conductor Type	CODE/FLEX

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	2960

## Product Assets

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog

Catalogs - BURNDY Master Catalog - Section C - Compression

Connections

Customer Notices - Prop 65 Notice

Interactive Catalog - BURNDY Full-Line Digital Catalog

Sales Drawings - SD..206624-01

Specifications - YCHC34TC34



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRDY-YCHC34TC34-SPEC-EN | REV 8/2024