

Compression C-Tap

By Burndy
Catalog # YCHC39TC31



Copper Compression C Tap, 750-500 kcmil (Main), 350 kcmil-2 AWG (Tap 1), 2-6 AWG (Tap 2), 8-14 AWG (Tap 3), Tin Plated.

Application

Wire Tap

General

Color Code	Blue
Connector Type	C-TAP
Die Index	1103
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YCHC Series
UPC	781810013786
UPC 12 Digit	7818100137866

Dimensions

Dimension - Height inch	2.96 in
Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.31 in
Dimension - Strip Length inch	1-3/8
Dimension - Width inch	1.53 in

Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper Flex I Run Range	500 kcmil
Conductor - Copper Flex K Run Range	500 kcmil
Conductor - Copper Flex M Run Range	500 kcmil
Conductor - Copper Str Run Range	750 KCMIL-350 KCMIL
Conductor - Copper Str Run Range	750 KCMIL-350 KCMIL
Conductor - Copper Str Tap Range	350 KCMIL-2 AWG
Conductor - Copper Str Tap Range	350 KCMIL-2 AWG
Conductor - Material	COPPER
Conductor Size	750 KCMIL-350 KCMIL
Conductor Type	CODE/FLEX

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	2400

Product Assets

[3D Models - YCHC39TC31_MODEL-IGES](#)
[3D Models - YCHC39TC31_MODEL-STEP](#)
[3D Models - YCHC39TC31_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..206624-01](#)

