



## Compression C-Tap

By Burndy  
Catalog # [YCHC39TC39](#)

Copper Compression C Tap, 750-500 kcmil (Main), 750-350 kcmil (Tap), Tin Plated.



### Application

Wire Tap

### General

Color Code	Blue
Connector Type	C-TAP
Construction Material - Main	Copper
Die Index	1103
EU RoHS Indicator	Contact Manufacturer
Finish Type	Tin-Plated
Insulation	N
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YCHC
UPC	781810013793
UPC 12 Digit	7818100137933

### Dimensions

Dimension - Height inch	3.12 in
Dimension - L Length Overall mm	27 mm
Dimension - Length Overall inch	1.06 in
Dimension - Strip Length inch	1-1/8
Dimension - Width inch	1.53 in

### Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

### Conductor Related

Conductor - Copper Flex I Run Range	500 kcmil
Conductor - Copper Flex I Tap Range	350 kcmil-500 kcmil
Conductor - Copper Flex K Run Range	500 kcmil
Conductor - Copper Flex K Tap Range	350 kcmil-500 kcmil
Conductor - Copper Flex M Run Range	500 kcmil
Conductor - Copper Flex M Tap Range	350 kcmil-500 kcmil
Conductor - Copper Str Run Range	750 KCMIL-350 KCMIL
Conductor - Copper Str Run Range	750 KCMIL-350 KCMIL
Conductor - Copper Str Tap Range	750 KCMIL-350 KCMIL
Conductor - Copper Str Tap Range	750 KCMIL-350 KCMIL
Conductor - Material	COPPER
Conductor Size	750 KCMIL-750 KCMIL
Conductor Type	CODE/FLEX

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	15
Minimum Pack Quantity	15
Pallet Quantity	3330

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD..206624-01](#)



A proud member of the Hubbell Family.