

# Compression C-Tap

By Burndy  
Catalog # [YCHC44TC44](#)



Copper Compression C Tap, 1000-750 kcmil (Main), 1000-750 kcmil (Tap), Tin Plated.

## Application

Wire Tap

## General

Color Code	White
Connector Type	C-TAP
Die Index	1102
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	CRIMPIT™
Type	YCHC Series
UPC	781810013748
UPC 12 Digit	7818100137488

## Dimensions

Dimension - Height inch	3.59 in
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.16 in
Dimension - Strip Length inch	1-1/4
Dimension - Width inch	1.73 in

## Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

## Conductor Related

Conductor - Copper Flex I Run Range	800 kcmil-1000 kcmil
Conductor - Copper Flex I Tap Range	800 kcmil-1000 kcmil
Conductor - Copper Flex K Run Range	800 kcmil-1000 kcmil
Conductor - Copper Flex K Tap Range	800 kcmil-1000 kcmil
Conductor - Copper Flex M Run Range	800 kcmil-1000 kcmil
Conductor - Copper Flex M Tap Range	800 kcmil-1000 kcmil
Conductor - Copper Str Run Range	1000 KCMIL-750 KCMIL
Conductor - Copper Str Run Range	1000 KCMIL-750 KCMIL
Conductor - Copper Str Tap Range	1000 KCMIL-750 KCMIL
Conductor - Copper Str Tap Range	1000 KCMIL-750 KCMIL
Conductor - Material	COPPER
Conductor Size	1000 KCMIL-1000 KCMIL
Conductor Type	CODE/FLEX

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	2400

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD..206624-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YCHC44TC44-SPEC-EN | REV 8/2023