

# Compression C-Tap

By Burndy  
Catalog # YCHC8TC8



Cu C-Tap compression connector, # 8-12(8-12)(Main),8-12(8-12) (Tap1), Tin plated, Red, 240 index.

## Application

Wire Tap

## General

Color Code	Red
Connector Type	C-TAP
Die Index	240
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	CRIMPIT™
Type	YCHC Series
UPC	781810013823
UPC 12 Digit	7818100138233

## Dimensions

Dimension - Height inch	0.53 in
Dimension - L Length Overall mm	13 mm
Dimension - Length Overall inch	0.56 in
Dimension - Strip Length inch	5/8
Dimension - Width inch	0.34 in

## Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

## Conductor Related

Conductor - Copper Str Run	8 AWG-12 AWG
Conductor - Copper Str Run Range	8 AWG-12 AWG
Conductor - Copper Str Tap	8 AWG-12 AWG
Conductor - Copper Str Tap Range	8 AWG-12 AWG
Conductor - Material	COPPER
Conductor Size	8 AWG-12 AWG
Conductor Type	CODE/FLEX

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	96000

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD..206624-01](#)